
DDR-2000S for Hydromat

7" Angle flange adaptor	σ
7" Butterfly Valve	6
7" Cut Pipe	IJ
7" Pipe	4
7" Adjustable Sleeve	ω
7″90 Degree Elbow	N
Standard is a 90 deg elbow	St
7" Plenum Box Optional	1
Parts Table	



Notesi

- 1) All clamps need to have a bead of silicone added to the sealing area (only needed for the Nordfab sysytem).
- All adjustable sleeves in the vertical position are to below the cut pipe. \Box -ringed go on the cut pipe and a bead of silicone
- needs to be placed between the \square -ring and the sleeve. 4) At points "A" Silicone angle flange adaptor to the
- Machine. 5) At point "B" Silicone Plenum Box to the Absolent.
- At point "C" ensure that the cover plate is installed screws installed from the outside into the cover plate on the insde of the Absolent with Silicone and the

